Data sheet

KOMET

KOMET® internal thread boring bar, right-hand Form 55°(Whitworth), Type: B03

Order data

Order number	240088 B03
GTIN	4047109017085
Item class	24H

Description

Version:
Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.
Sizes with suffix **L = extended shank.**
Tool material:
HSS/Co10 – for difficult to machine materials.
Note:
For suitable boring bar holders see No. 240070 and No. 240072.

Technical description

Boring depth	26 mm
for pitches	16–50 threads/inch
Type	B03
for bores from ∅	7 mm
Overall length	65 mm
Shank ∅	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning