




Safety coupling Stream-Line, Hose connection internal Ø (nominal bore): 8mm



Order data

Order number	080297 8
GTIN	7391390285300
Item class	08A

Description

Version:

Stream-Line hose adapter simply and effectively clamps the hose on to the coupling by means of a threaded nut - no hose clip required.

The **eSafe safety coupling** satisfies the ISO standard 4414 and EN 983 It is first depressurised and then decoupled in a second step (no whiplash). New improved single-handed operation.

Steel couplings have many advantages in pneumatic systems compared to standard brass couplings:

- **Easy to use with only one hand with low coupling force.**
- **High flow rate as a consequence of very low pressure drop.**
- **Long working life due to surface treatment and hardened components with tight manufacturing tolerances.**
- **Cost-effectiveness - the amortisation time is 2 years at the most.**

Rate of flow: 2250 ltr/min, maximum operating pressure 16 bar.

Application:

For improving the performance, economics, and safety of industrial compressed air installations.

Note:

The CEJN series 320 satisfies Euro standard 7.6 (nominal Ø 7.6 mm, Euro profile) and is compatible with all popular systems.

Technical description

Hose connection internal Ø (nominal bore)	8 mm
Type of product	Coupling

