

**Torx® key L-wrench, with knurling, Torx® profile: TX8****Order data**

|              |               |
|--------------|---------------|
| Order number | 625037 TX8    |
| GTIN         | 7610733281855 |
| Item class   | 63D           |

**Description****Version:**

L-shank; through hardened (hard and tough). PB Swiss Tools special steel combining maximum hardness with exceptional toughness. Surface nickel-plated and chrome-plated. Black tip.

**Advantage:**

The knurling to ISO 13444 type B increases the grip in wet or oily environments and thus enhances safety.

**Technical description**

|                            |                               |
|----------------------------|-------------------------------|
| Stock length               | 103×20 mm                     |
| Torx® profile              | TX8                           |
| Drive profile              | Screwdriver for TORX® screws  |
| Material                   | PB Swiss Tools special alloy. |
| Type of shank              | angled                        |
| Surface                    | chrome-plated                 |
| Point                      | black                         |
| Ball point on the long arm | no                            |
| Type of product            | Screwdrivers                  |