

**PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8 × 12 mm, usable hose length: 8m****Order data**

Order number	080240 8
GTIN	7391390134486
Item class	08A

Description**Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant from -20 / 60 °C. PU coiled hose 1/4 inch with eSafe steel safety coupling Ø 8×12 mm 8 m ISO B.

Supplied with:

Safety steel coupling No. 080285 and steel coupling adaptor No. 080290 included.

Technical description

Material	PU spiral hose
Hose external Ø	12 mm
usable hose length	8 m
Hose internal Ø	8 mm
maximum operating pressure	10 bar
Connection plug nipple	1/4 in
Connection quick-release coupling	1/4 in
Colour	blue
maximum bursting pressure	35 bar

Type of product

Hose

AccessoriesSafety shut-offExternal thread Connection external thread
1/4 in

080285 1/4

Coupling adaptor with external thread5-piece set
Connection external thread 1/4 in

080290 1/4