

**Garant****GARANT Master Mute boring bar shank HSK-T vibration damping, HSK-T 63,  
Shank Ø / usable length L1: 16/96mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 265060 16/96  |
| GTIN         | 4069515026291 |
| Item class   | 29E           |

**Description****Version:**

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

**Suitable for:**

GARANT Master Mute exchangeable cutting heads No. 265100 – 265377.

**Note:**

The usable length is extended by the length L of the respective exchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

**Technical description**

|                            |             |
|----------------------------|-------------|
| Overhang dimension A       | 152 mm      |
| Shank Ø                    | 16 mm       |
| Assembly bolt set          | 269026 1    |
| Series                     | Master Mute |
| Number of coolant channels | 3           |
| Adapter                    | HSK-T 63    |
| Vibration                  | damped      |
| Arbor standard             | ISO 26623-1 |
| Arbor standard             | ISO 12164-3 |

Data sheet

|                 |                   |
|-----------------|-------------------|
| Through-coolant | yes               |
| Type of product | Boring bar shanks |