Garant

Vario Plus Eco blade carrier, concave for face grooving, right-hand, Ø range for groove D1 / D2: 26/39mm

Order data

Order number	274518 26/39
GTIN	4067263950813
Item class	21U

Description

Version:
Optimised system stability thanks to multiple screw clamping and form fit.
Suitable for:
Toolholder No. 274500 – 274503, 274530, 274531.
Attention:
Without clamping screws (these are supplied with the toolholders).
Note:
D_1 = minimum Ø for the first first groove / D_2 = minimum Ø for the second groove.

Technical description

maximum 1st groove Ø D_2	39 mm
minimum 1st groove Ø D_1	26 mm
suitable indexable insert	No. 273664 – 273786
Series	Vario plus Eco

maximum cutting depth t_{max}	18 mm
Application type	right-hand
Through-coolant	yes
Groove width w	3 mm
Type of product	Cartridges