



**GARANT Master Mute boring bar shank PSC vibration damping, PSC 40,  
Shank Ø / usable length L1: 32/230mm**



### Order data

Order number	265062 32/230
GTIN	4069515026581
Item class	29E

### Description

**Version:**

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

**Suitable for:**

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

**Note:**

The usable length is extended by the length L of the respective interchangeable cutting head.  
Use **only with internal cooling** (temperature resistance of up to max. 100°C).

### Technical description

Assembly bolt set	269026 5
Overhang dimension A	266 mm
Shank Ø	32 mm
Reach L <sub>1</sub>	230 mm
Series	Master Mute
Number of coolant channels	3
Adapter	PSC 40
Vibration	damped
Arbor standard	ISO 26623-1

## Data sheet

Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar shanks