

Garant GRIDLINE

Computer workstation, Type: GB



Order data

Order number	948131 GB
GTIN	4062406073947
Item class	9GS

Description

Version:

The **keyboard drawer** snaps into place in full travel position, can be locked. With bamboo palm rest and cable strain relief. Top extension with keyboard drawer with perforated panel at side □ 9×9 mm at 37 mm intervals for mounting GARANT easyFix hooks and holders. **Computer housing** with **fan**, adjustable galvanised storage shelf and fixed storage shelf of bamboo.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Depth	500 mm
Weight	69 kg

Data sheet

Depth in G	20
Height	1020 mm
Width in G	30
Width	750 mm
Support cabinet usable height	645 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
Power supply	Mains operated
#Plug type, input	G
Nominal voltage	250 V
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 degrees
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Computer workstation

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948131-GB>