

Garant GRIDLINE

Computer terminal, Type: DE



Order data

Order number	948101 DE
GTIN	4062406073602
Item class	9GS

Description

Version:

TFT monitor housing for flat screen. Storage shelf made of bamboo. Computer housing fitted with fan and an adjustable galvanised storage shelf.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Supplied with:

The integral **electrical installation** includes a multiple socket outlet (6-way 250 V/16 A with ON/OFF switch), connection cable 1.2 m.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Footrests are **always** RAL 7016 anthracite grey **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	73 kg
--------	-------

Width	750 mm
Width in G	30
Monitor housing usable depth	230 mm
Height	1620 mm
Depth in G	20
Monitor housing usable height	460 mm
Depth	500 mm
Monitor housing usable width	690 mm
Support cabinet usable height	845 mm
Support cabinet usable width	700 mm
IP Index of Protection	IP 41
Power supply	Mains operated
Nominal voltage	250 V
#Plug type, input	F
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Computer desk

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948101-DE>