

Garant**180° reverse countersinking mill, Countersink Ø D: 18mm****Order data**

Order number	217180 18
GTIN	4045197196903
Item class	210

Description**Version:**

With just one cutter (z = 1). Without internal cooling.

Note:

Dimension e = programming dimension (information on the end face). Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Countersink Ø D	18 mm
Number of cutting edges Z	1
Overhang L ₁	62 mm
Minimum Ø d _{min}	10.5 mm
Collar Ø D ₁	25 mm
L ₃	40 mm
Insert screw	219795 1 (8IP; 1.2 Nm)

Data sheet

Shank Ø D _s h6	20 mm
L ₂	47 mm
Shank type	Whistle Notch
Programming dimension e	4.05 mm
suitable indexable insert	260142
Overall length L	112 mm
Countersink angle	180
Tool exchange	PowerCard
Type of product	Counterbores, countersinks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/217180-18>