

**Garant****Garment locker with rotary catch, Number of compartments: 6****Order data**

Order number	949015 6
GTIN	4062406073107
Item class	91G

**Description****Version:**

Feet of 2 mm thick aluminium sheet. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Hanger rail with 3 hooks per compartment.

**Standard:**

**DIN 4547**

**Colour:**

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Note:**

Optionally with a plinth panel. Please contact us.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

**Technical description**

Nameplate	yes
Weight	102 kg

Standard	DIN 4547
Special paints available	yes
Number of compartments	6
Support cabinet version	Aluminium feet
usable width of each compartment	342 mm
Depth	520 mm
Lock version	Rotary catch
Ventilation slots in the door	no
Height	1850 mm
Width	1200 mm
usable height of each compartment	780 mm
for padlock	yes
suitable for integral helmets	yes
Cabinet fronts	Plain sheet metal swing door
Number of clothes rails	1
usable depth of each compartment	472 mm
for padlock with shackle Ø up to	6 mm
Sloping roof	no
Ventilation slots in the back wall	yes
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Locker

## Accessories

Precision cylinder padlock with lock barrel, shared key Body  
Ø 45 mm

085812 45

Precision cylinder padlock with lock barrel, individual keys Body Ø 45 mm	085814 45
Precision cylinder padlock without lock barrel Body Ø 45 mm	085816 45
Precision cylinder lock with high shackle individual keys Body Ø 40 mm	085875 40
Rotary catch Type R	914190 R
Base fascia, front Type 1200	958737 1200
Base fascia side Type 520	958738 520