



LED ring light with segment control



Order data

Order number	492230
GTIN	4045197330192
Item class	49K

Description

Version:

Neutral white light (40 LEDs, light temperature 5900K), continuously dimmable. Segment selection (1/4 circle) and rotation (left/right) for optimum contrast conditions. Homogeneous illumination and flicker-free operation due to DC power supply. LED working life 25,000 hours. ESD socket for dissipating static electrical charges. Sturdy slim design of the lighting head, internal Ø 66 mm, including the adaptor.

Supplied with:

Including control unit, international switched-mode power supply (100 - 240 V) and adaptor from Ø 66 mm to 58 mm.

Optional extras:

Accessory parts adapter Ø 66 mm to 60 mm No. 492232 size 66/60, diffuser No. 492232 size DIFF, polarisation filter set No. 492232 size FILTER.

Note:

Adapters for lenses with other Ø (Zeiss, Leica, Nikon) available on request.

Technical description

Power supply	Mains operated
Ring lamp Ø	66 mm
Colour temperature	5900 K
Ring lamp height	25 mm
Type of product	Lighting unit for measuring tool

Accessories

Accessories for LED ring light Type FILTER	492232 FILTER
Accessories for LED ring light Type LIGHT	492232 LIGHT
Accessories for LED ring light Type 66/60	492232 66/60
Accessories for LED ring light Type DIFF	492232 DIFF