Data sheet

Garant

Steel boring bar A.. SVJBR 142°, for indexable inserts VB.., right-hand

Order data

Order number	261124 16/11
GTIN	4045197778369
Item class	21T

Technical description

Set of insert screws	269028 7
Clamping height L_2	15 mm
ISO code toolholder	A16M SVJBR/L11
Head length L_1	31.4 mm
Overall length L	150 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Minimum pre-drill ∅ D_{min}	22 mm
Neck width L_4	9.5 mm
Setting angle κ	142 degrees
Centre offset L_3	2 mm

Shank ∅ D_s	16 mm
Standard	Works standard
Through-coolant	yes
Application type	right-hand
Boring depth up to	3×D
Shank type	Steel
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar

Suitable products

https://www.hoffmann-group.com/GB/en/hom/p/261124-16/11