Data sheet

Garant

Heavy-Duty-Plus blade carrier for face grooving, right-hand, ∅ range Groove D1 / D2: 114/160mm

Order data

Order number	274084 114/160
GTIN	4062406204464
Item class	21U

Description

Version:
For grooving inserts No. 275021 – 275048.
Application:
In conjunction with toolholder No. 274006.
Attention:
Without clamping screws (these are supplied with the toolholders). The assembly key No. 279940 1-3 must be ordered separately.
Note:
D_1 = minimum ∅ for the first groove / D_2 = maximum ∅ for the first cut.
D_2 = 999 in the size designation corresponds to theoretically infinite.

Technical description

maximum cutting depth t_{max}	100 mm
maximum 1st groove ∅ D_2	160 mm
minimum 1st groove ∅ D_1	114 mm
Application type	right-hand
System key	yes
Groove width w	8 mm
Type of product	Cartridges