

Garant**Open ended spanner / ratchet ring spanner, Width across flats: 10mm****Order data**

Order number	GG6038 10
GTIN	4069515050661
Item class	GGN

Description**Version:**

Drop forged. Ring end with especially smooth-running, robust ring ratchet. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Supplied with:

5 pieces open ended / ratchet ring spanner No. 614770 10.

Technical description

Ring Ø D	20.8 mm
Spanner length L	160 mm
Ring thickness h ₂	7.7 mm
Jaw width b	22 mm
Jaw height h ₁	4.8 mm
Width across flats	metric

Data sheet

Width across flats	10 mm
Ring setting	0 degrees
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chromium vanadium steel
Surface	chrome-plated
End stop at jaw	no
Stop function at jaw	no
with swivel head	no
Ratchet reversible	no
Type of product	Spanners
USP1	5 pieces open ended spanner / ratchet ring spanner

Suitable products

No Shop URL available for: GG6038 10