Holder for burnishing roller Swivelling head, right-hand, Shank size: 10-16

Order data

Order number	291416 10-16
GTIN	4030741083167
Item class	29M

Description

Version:
Swivelling tool head (adjustment range ± 90°).
Advantage:
Surface quality up to R_z 2 µm possible.
Application:
For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.
For roller-burnishing of **uninterrupted contours** (convex, concave, cylindrical and conical) and flat faces. Suitable even for applications up to the collar.
Supplied with:
Shank size 10 including shank adaptor 12 mm × 12 mm and 16 mm × 16 mm.
Attention:
Burnishing rollers must be ordered separately!
Note:
For detailed application recommendations please see the instruction handbook supplied.
Check potential interference contours (x dimension of the roller = 2.5 mm).

Technical description

Product name attribute	right-hand
Type of product	Smooth rolling tool