



Value pack fibre disc standard aluminium oxide (A)



Order data

Order number	GG5651 24
GTIN	4045197296054
Item class	GGN

Description

Version:

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. **HOLEX universal fibre disc** for grinding all metals. Grit type: **Aluminium oxide (A)**. same as 566510.

Version of the advertising text:

General-purpose fibre discs with tear-resistant, very pliable vulcanised fibre. Bore Ø 22.23 mm with cross slits. Grit type: Regular aluminium oxide (A) (**same as 566410, 566510, 566610**). For grinding all metals, wood and plastics.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Content:

250 pieces / bulk pack.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

Disc Ø	125 mm
Grit	24
Contents	250

Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
Adapter	Roloc™ quick-change system
Bore Ø	22.23 mm
suitable for quick-change system	Roloc™
optimised for material	Steel
maximum circumferential speed	80 m/s
maximum speed	12200 min ⁻¹
USP1	Fibre disc standard aluminium oxide (A)

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

Accessories

Fibre disc Aluminium Oxide(A) Grit 24

566510 24