



Value pack LED torch with rechargeable battery



Order data

Order number	GG1363 150
GTIN	4067263138037
Item class	GGN

Description

Version:

Sturdy, rechargeable LED torch made of anodised aluminium. **The 2 settings** with additional **boost function** provide **outstanding light output** for all applications. The single-hand focussing enables quick and easy adjustment of the beam.

- **Charging and discharge monitoring by means of coloured LED in the switch.**
- **Long running time with constant light output.**
- **USB-C charging socket.**
- **Anti-roll protection.**
- **With focussable lamp head.**

Feature:

Contents 4 pieces

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and battery. With hand loop.

Note:

For suitable replacement batteries see No. 081365

Technical description

Light current boost	700 lm
Power supply	Mains operated
Bulb	LED lamp
Illumination time	1.5 h
Head Ø	28 mm
Battery voltage	3.7 V
IP Index of Protection	IP 54
Weight	95 g
Overall length	144 - 154 mm
Type of rechargeable battery	Lithium-ion
Illumination	400 lm
Illumination time boost	30 s
Number of rechargeable batteries contained	4
Illumination step 2	140 lm
Torch function	Focus
CRI value	>80
Battery capacity	1.6 Ah
Replaceable battery	yes
Illumination time stage 2	5 h
Type of product	Flashlight

Accessories

LED torch with rechargeable battery Type 150	081363 150
Replacement battery 16650	081365 16650