

Garant

LED cordless work light, Type: 200



Order data

Order number	081441 200
GTIN	4062406232900
Item class	01A

Description

Version:

Versatile LED cordless work light in slim sturdy design with a wide range of applications. Practical monitoring of the state of charge of the battery by LED display directly on the light.

- **Main light steplessly dimmable from 10 - 100 %.**
- **Integral spotlight function.**
- **Flexible use thanks to 180° pivoting magnetic base, together with fold-up and rotating suspension hook.**

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable and plug-in power supply unit.

Note:

For mounting on GARANT easyFix perforated panels, also order the base plate No. 955820 size 2.

Technical description

Overall length	200 mm
----------------	--------

Data sheet

Number of rechargeable batteries contained	1
Weight	157 g
Illumination	20 - 200 lm
Power supply	Rechargeable battery-powered
IP Index of Protection	IP 65
Battery voltage	3.7 V
ATEX zone	no
Overall width	39 mm
Battery capacity	1.2 Ah
Illumination time	2 - 20 h
Bulb	LED module
Type of rechargeable battery	Lithium-ion
Type of product	Work lamp

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/081441-200>