Data sheet

Garant UNI LINE

GARANT Uni Line ESD Cleaning Wall wheeled, Type: M

Order data

Order number	972890 M
GTIN	4067263126126
Item class	9GD

Description

Version:
Very sturdy, double-walled, ESD-compliant column made from sheet metal, perforated panels that can be used on both sides ☐ 9×9 mm on a 37 mm grid for attaching perforated panel accessories and GARANT easyFix hooks and holders. Sturdy base plate permits easy set up and movement. **Electrically conductive wheels** with 4 castors ∅ 125 mm, 2 with parking brake.
Supplied with:
GARANT Uni Line ESD Wall mobile; ESD easyBin recycling collection bin No. 972910 size 25; ESD open storage bin No. 972321 size AB1 with GARANT easyFix box holder; GARANT easyFix toolholder 90°, 100 mm long; GARANT easyFix toolholder double 45°, 100 mm long; GARANT easyFix bottle/can holder with inner ∅ of 90 mm.
Colour:
Similar to RAL 7035 light grey **ESD powder-coated. Not configurable.**

Technical description

Number of castors with parking brake	2
Wheel ∅	125 mm
Depth	750 mm

Height	2067 mm
Number of castors without parking brake	2
Weight	69 kg
Usable width	600 mm
Width	600 mm
Safe working load	75 kg
Series	Cleaning Wall
Hoffmann perforated panel grid interval	9×9 mm
electrostatic characteristic	EGB/ESD
Type of product	Cleaning station

Suitable products

https://www.hoffmann-group.com/GB/en/hom/p/972890-M