



## GARANT Master Mute boring bar shank vibration damping, Shank Ø / overall length L: 50/518



### Order data

|              |               |
|--------------|---------------|
| Order number | 265076 50/518 |
| GTIN         | 4069515037471 |
| Item class   | 29E           |

### Description

#### Version:

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

#### Supplied with:

Reducing adaptor for coolant connection.

#### Note:

Do not clamp on the area marked S!  $D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$ .  
Usable length = overall length L minus clamping length (recommended =  $3 \times D$ ). Use **only with internal cooling** (temperature resistance of up to max. 100°C).

### Technical description

|                             |             |
|-----------------------------|-------------|
| Overall length L            | 518 mm      |
| Centre offset H base body   | 5 mm        |
| non-clamping range S        | 187 mm      |
| Assembly bolt set           | 269026 3    |
| recommended clamping length | 150 mm      |
| Shank Ø                     | 50 mm       |
| Version                     | Steel       |
| Number of coolant channels  | 1           |
| Series                      | Master Mute |
| Vibration                   | damped      |

|                 |                   |
|-----------------|-------------------|
| Through-coolant | yes               |
| Type of product | Boring bar shanks |

**Suitable products**

<https://www.hoffmann-group.com/GB/en/hom/p/265076-50/518>