

Garant**Master Mute boring bar A.. SDUCL 93°, for indexable inserts DC.., left****Order data**

Order number	265015 10/07
GTIN	4069515024730
Item class	29E

Description**Version:**

Round shank without clamping face. Carbide-reinforced shank.

Note:

Boring bar can be shortened as far as length L_{min} . Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank $\varnothing D_s$	10 mm
Series	Master Mute
Overall length L	161 mm
Overhang L_1	110 mm
Minimum pre-drill $\varnothing D_{min}$	15 mm
Insert size	7 mm
ISO code toolholder	A10X SDUCR/L07
Standard	Works standard
Set of insert screws	269028 38
Centre offset L_3	9 mm
suitable indexable insert	DC.. 0702..
Setting angle κ	93 degrees
Application type	left-hand

Data sheet

Shank type	Steel
Vibration	damped
Through-coolant	yes
Application	Internal longitudinal turning
Application	Facing
Type of product	Boring Bar