

**Torch LED and UV with rechargeable battery, Type: UV-LED****Order data**

Order number	081518 UV-LED
GTIN	4045197967251
Item class	02A

Description**Version:**

Rechargeable anodized aluminium LED torch with battery, 3-stage LED, **switchable to UV light**, **90° rotating head** and magnetic base. Latest LED technology with outstanding lighting power.
· **Rubber cover for the operating button.**

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Supplied with USB-C charging cable.

Technical description

Battery capacity	2.6 Ah
Illumination step 2	300 lm
IP Index of Protection	IP 54
Illumination	450 lm
Illumination time	2 - 8 h
Head Ø	29 mm
Wavelength of UV radiation	395 nm
Number of rechargeable batteries contained	1
Overall length	158 mm
Type of rechargeable battery	Lithium-ion

Power supply	Rechargeable battery-powered
Illumination step 3	120 lm
Type of product	Flashlight