



### Pressure regulator 0.5 –10 bar, Internal thread Ø: 1/4in



#### Order data

Order number	080012 1/4
GTIN	4047322129398
Item class	08A

#### Description

**Version:**

Service units can be made up as required; the coupling pack supplied can be used to add extensions.

**Service unit** in modular series ("multifix" system), consisting of filter, pressure regulator and mist atomiser. Control range 0.5- 10 bar, operating pressure maximum 16 bar, operating temperature maximum 60 °C.

**Advantage:**

The service unit can be configured individually, e. g. with several pressure regulators, without oil atomiser (for oil-free tools) etc.

**Application:**

For systems in the pressure range up to 16 bar. Compatible with the products of CEJN, RECTUS and JW. L.

**Supplied with:**

1 pressure regulator with G1/4 inch internal thread.

#### Technical description

Overall length (L) as 3-part service unit	138 mm
---	--------

## Data sheet

Height (H)	190 mm
Flow rate for 3-part service unit	1150 l/min
Internal thread Ø	G1/4 in
Type of product	Pressure regulator