



## Value pack fibre disc standard aluminium oxide (A)



### Order data

Order number	GG5651 40
GTIN	4045197296061
Item class	GGN

### Description

**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots.

**HOLEX universal fibre disc** for grinding all metals. Grit type: **Aluminium oxide (A)**.

same as 566510.

**Version of the advertising text:**

General-purpose fibre discs with tear-resistant, very pliable vulcanised fibre. Bore Ø 22.23 mm with cross slits. Grit type: Regular aluminium oxide (A) (**same as 566410, 566510, 566610**). For grinding all metals, wood and plastics.

**Application:**

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 566670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

**Content:**

250 pieces / bulk pack.

**Note:**

**Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.**

### Technical description

Grit	40
Disc Ø	125 mm
Contents	250

Grinding media	Regular aluminium oxide (A)
Grinding medium code	A
Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
Adapter	Roloc™ quick-change system
Bore Ø	22.23 mm
suitable for quick-change system	Roloc™
optimised for material	Steel
maximum circumferential speed	80 m/s
maximum speed	12200 min <sup>-1</sup>
USP1	Fibre disc standard aluminium oxide (A)

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		

---

## Accessories

Fibre disc Aluminium Oxide(A) Grit 40

566510 40