

Garant**Value pack surface sealant 5GP73****Order data**

Order number	GG8068 50
GTIN	4067263136491
Item class	GGN

Description**Version:**

Sealant that cures when applied as a hermetic seal between close-fitting metal surfaces. Type **5GP73**. Medium-strength thixotropic surface seal for sealing metallic threaded parts. Sealing of covers, flanges and surfaces. Quick-curing, slightly flexible sealant film.

Feature:

Contents: 3 pieces

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Colour	green
Chemical basis	anaerobic methacrylate
Operating temperature range	-55 - 180 °C
Strength class	medium strength
Dynamic viscosity	35000 - 60000 mPas

Shape	liquid
Flashpoint	100 °C
Capacity	50 ml
Suitable for application area	Liquid gasketing
Suitable for application area	Flange connection
Working life after date of manufacture	24 mo
Suitable for material	Metal
Characteristics	fluorescent under UV light
Characteristics	water-resistant
Characteristics	oil-resistant
Density	1.11 g/cm ³
Storage temperature	5 - 23 °C
Sustainability	GARANT GreenPlus
minimum break-away torque	10 - 20 Nm
Series	GreenPlus
Touch dry after	5 - 15 min
Maximum gap size	0.2 mm
Functional strength to	3 - 6 h
Type of product	Sealant

Accessories

GARANT GreenPlus surface sealant5GP73 Contents 50 ml

088068 50