

**PU coiled hose 1/2 inch with eSafe steel safety coupling Ø 11 × 16 mm, usable hose length: 8m****Order data**

Order number	080249 8
GTIN	7391390305473
Item class	08A

Description**Version:**

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention. Temperature-resistant between - 20/+ 60°C. Maximum operating pressure 16 bar. Complies with ISO standard B.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

maximum bursting pressure	35 bar
Connection plug nipple	1/2 in
Material	PU spiral hose
Hose external Ø	16 mm
Connection quick-release coupling	1/2 in
usable hose length	8 m

Hose internal Ø	11 mm
maximum operating pressure	10 bar
Colour	blue
Type of product	Hose

Accessories

Safety coupling External thread 1/2 in	Connection external thread 080276 1/2
--	--