

**TRICOFLEX****Braided hose, blue plasticised PVC, Length 50 m, Hose internal Ø: 9mm****Order data**

Order number	080036 9
GTIN	3506111047325
Item class	08A

**Description****Version:**

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.

Super Nobelair Soft, **due to Full-Soft technology highly flexible** even at low temperatures. For use indoors and outdoors. Operating pressure 15 bar.

**Technical description**

Material	PVC hose, three-layer with polyester fibre reinforcement
Temperature range	-15 - 60 °C
Colour	blue
Hose external Ø	15 mm
Hose internal Ø	9 mm
Hose length	50 m
maximum operating pressure	15 bar
Product name attribute	Length 50 m
Type of product	Hose

