



## PU coiled hose 1/2 inch with eSafe steel safety coupling Ø 11 x 16 mm, usable hose length: 6m



### Order data

Order number	080241 6
GTIN	7391390097484
Item class	08A

### Description

#### Version:

Very light, flexible, and abrasion-resistant PU spiral hose with good spring retention.  
Temperature-resistant from -20 / 60 °C.

#### Supplied with:

Includes quick-release **safety** coupling No. 080285 and steel coupling adaptor No. 080290.

### Technical description

usable hose length	6 m
Material	PU spiral hose
maximum operating pressure	10 bar
Connection plug nipple	1/2 in
Hose internal Ø	11 mm
Connection quick-release coupling	1/2 in

Hose external Ø	16 mm
Colour	blue
maximum bursting pressure	35 bar
Type of product	Hose

---

## Accessories

Safety shut-off	External thread	Connection external thread	080285 1/2
1/2 in			
Coupling adaptor with external thread	5-piece set		080290 1/2
Connection external thread 1/2 in			