

Garant**Garment locker with rotary catch, Number of compartments: 6****Order data**

Order number	949026 6
GTIN	4069515040563
Item class	91G

Description**Version:**

The body of the garment locker has plastic slides in the base frame and a removable plinth panel at the front. Back walls with ventilation slots, doors with towel holder and name plate. The door can easily be converted from right- to left-hinged.

With rotary catch; lockable with a padlock (not included in delivery).

Hanger rail with 3 hooks per compartment.

Standard:

DIN 4547

Colour:

Body light grey RAL 7035, doors anthracite RAL 7016, **powder-coated.**

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

for padlock	yes
Height	1850 mm

Data sheet

Special paints available	yes
Width	1200 mm
Cabinet fronts	Plain sheet metal swing door
Depth	520 mm
Lock version	Rotary catch
Number of clothes rails	1
Ventilation slots in the back wall	yes
suitable for integral helmets	yes
for padlock with shackle Ø up to	6 mm
usable height of each compartment	780 mm
Number of compartments	6
usable width of each compartment	342 mm
usable depth of each compartment	472 mm
Weight	102 kg
Sloping roof	no
Support cabinet version	Aluminium feet
Standard	DIN 4547
Ventilation slots in the door	no
Nameplate	yes
Material thickness	0.9 mm
Door opening angle	225 degrees
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Garment locker

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/949026-6>