



Value pack quick-change hose coupling



Order data

Order number	GG0172 6
GTIN	4067263138112
Item class	GGN

Description

Version:

Quick-release couplings nominal value 7.2. Flow rate 1000 l/min (air). Brass material (bright finish). Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Feature:

Contents 10 pieces

Technical description

Hose internal thread connection Ø	6 mm
Flow rate	1000 l/min
maximum operating pressure	35 bar
Type of product	Coupling

Accessories

Quick connect
connection Ø 6 mm

With hose connection
Hose internal thread

080172 6