



### "Revo KRE" body clamp, Jaw capacity a: 600mm



#### Order data

|              |               |
|--------------|---------------|
| Order number | 860291 600    |
| GTIN         | 4008158040134 |
| Item class   | 83K           |

#### Description

##### Version:

Beam of bright drawn steel, electro-galvanised. Moving jaw with double anti-slip protection. Smooth running steel spindle with trapezoidal thread, burnished. Metal, reinforced plastic housing. Clamping forces up to **8000 N**.

- **Extremely large clamping faces with removable protective caps**
- **Workpiece protection inserts, removable**
- **Turning the bottom jaw over converts the clamp into a spreader**
- **2-component handle with hex socket (6 AF) for easy application of the clamping force**

##### Application:

The jaws surround the beam, thus can be used to clamp at the sides and the rear. This allows access to clamping positions inaccessible to conventional clamps. Can be converted to spreading, **no tools required**.

##### Note:

**Successor product to No. 860290.**

#### Technical description

|        |         |
|--------|---------|
| Weight | 2.76 kg |
|--------|---------|

## Data sheet

|                                 |              |
|---------------------------------|--------------|
| Spreading width e               | 255 - 730 mm |
| Cross section of the slide rail | 29×9 mm      |
| Jaw capacity a                  | 600 mm       |
| Throat b                        | 95 mm        |
| Manufacturer's designation      | REVO KRE     |
| maximum clamping force          | 8000 N       |
| Type of product                 | Clamp        |