



Value pack pot magnet with keeper plate



Order data

Order number	GG5940 27
GTIN	4067263137757
Item class	GGN

Description

Version:

- Machining the steel jacket will not impair magnet performance.
- Magnetic force directed downwards as cased in an aluminium ring.
- Tapped hole in the magnet top face, for fastening.
- Magnetic material temperature-resistant up to maximum 220°C.

Feature:

Contents: 10 pieces

Application:

Incorporation in jigs, for holding or lifting.

Technical description

Nominal clamping force	61 N
maximum temperature resistance	220 °C
Height	25 mm
Tapped attachment hole in the magnet head	M6 mm
Material of the surface	Stone
Ø	27 mm

Material of the magnet core	AlNiCo
Type of product	Pot magnet

Accessories

Pot magnet with keeper plate Ø 27 mm	085940 27
--------------------------------------	-----------