

Garant GRIDLINE

Computer workstation with printer flap, Type: GB**Order data**

Order number	948122 GB
GTIN	4062406073886
Item class	9GS

Description**Version:**

TFT monitor housing for flat screens, with fixed storage compartment for cables. Computer housing with fan in the housing cover and an adjustable shelf. Lockable keyboard drawer with palm rest of bamboo, height adjustable in 3 steps at 60-mm spacing. Keyboard drawer locks in full travel position. Storage shelf made of bamboo.

Function:

IP41: Protected against water falling vertically and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Colour:

Body RAL 7035 light grey, doors and drawers RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	750 mm
Weight	82 kg
Monitor housing usable depth	230 mm
Depth in G	20

Depth	500 mm
Monitor housing usable height	460 mm
Dimensions printer flap	236×290 mm
Width in G	30
Height	1740 mm
Monitor housing usable width	690 mm
Support cabinet usable width	700 mm
Support cabinet usable height	645 mm
IP Index of Protection	IP 41
Power supply	Mains operated
On/Off switch	yes
#Plug type, input	G
Nominal voltage	250 V
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

Accessories

Slide handle for garment lockers without cylinder insert	914221
Slide handle for GridLine Type GP11	914226 GP11