

Garant**GARANT Master Mute boring bar shank HSK-T vibration damping, HSK-T 63,
Shank Ø / usable length L1: 32/170mm****Order data**

Order number	265060 32/170
GTIN	4069515026352
Item class	29E

Description**Version:**

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Suitable for:

GARANT Master Mute exchangeable cutting heads No. 265100 – 265377.

Note:

The usable length is extended by the length L of the respective exchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank Ø	32 mm
Overhang dimension A	226 mm
Assembly bolt set	269026 5
Series	Master Mute
Number of coolant channels	3
Adapter	HSK-T 63
Vibration	damped
Arbor standard	ISO 26623-1
Arbor standard	ISO 12164-3

Through-coolant	yes
Type of product	Boring bar shanks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265060-32/170>