



Value pack industrial coupling external thread



Order data

Order number	GG0230 1/4
GTIN	4067263138235
Item class	GGN

Description

Version:

Industrial coupling designed for an optimised high flow rate of 2000 l/min (air), **nominal value 7.8**. High-quality and sturdy quick-release coupling that shuts off on one side. Flow-optimised valve, extremely high flow rates, low pressure drop, long service life, excellent operational reliability and absolute leak-tightness.

Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Feature:

Contents 5 pieces

Material:

Nickel-plated brass, sleeve steel hardened and nickel-plated.

Technical description

Material	Brass
Connection external thread	1/4 in
maximum operating pressure	35 bar
Flow rate	2000 l/min

Type of product

Coupling

Accessories

Industrial coupling External thread Connection external
thread 1/4 in

080230 1/4