

**Industrial coupling Internal thread, Connection internal thread: 1/2in****Order data**

Order number	080231 1/2
GTIN	4062406423131
Item class	02A

Description**Version:**

Industrial coupling designed for an optimised high flow rate of 2000 l/min (air), **nominal value 7.8**. High-quality and sturdy quick-release coupling that shuts off on one side. Flow-optimised valve, extremely high flow rates, low pressure drop, long service life, excellent operational reliability and absolute leak-tightness.

Operating pressure: PN 35 bar / temperature: -20 °C to +100 °C.

Material:

Nickel-plated brass, sleeve steel hardened and nickel-plated.

Technical description

maximum operating pressure	35 bar
Material	Brass
Connection internal thread	1/2 in
Flow rate	2000 l/min
Type of product	Coupling