

**PU braided hose, blue, Length 50 m, Hose internal Ø (nominal bore): 8mm****Order data**

Order number	080220 8
GTIN	7391390087850
Item class	08A

Description**Version:**

Very light, flexible, and abrasion-resistant PU hose. Outstanding resistance to oil, solvents, and non-aqueous solvents. Operating pressure 16 bar.

Hose with polyester fibre reinforcement. Temperature range -15 °C to 60 °C.

Technical description

Hose internal Ø (nominal bore)	8 mm
Material	PU braided hose
maximum operating pressure	16 bar
Hose length	50 m
Colour	blue
Hose external Ø	12 mm
Product name attribute	Length 50 m
Type of product	Hose

Accessories

Safety shut-offStream-Line Hose connection internal Ø
(nominal bore) 8 mm

080297 8