

Garant**GARANT Master Mute boring bar shank vibration damping, Shank Ø / overall length L: 32/416****Order data**

Order number	265076 32/416
GTIN	4069515037426
Item class	29E

Description**Version:**

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Supplied with:

Reducing adaptor for coolant connection.

Note:

Do not clamp on the area marked S! $D_{\min} = 1/2 \text{ shank } \varnothing + H + \text{cutting head centre-line offset } L_3$.
Usable length = overall length L minus clamping length (recommended = $3 \times D$). Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Assembly bolt set	269026 5
Shank Ø	32 mm
Overall length L	416 mm
recommended clamping length	96 mm
non-clamping range S	151 mm
Version	Steel
Number of coolant channels	3
Series	Master Mute
Vibration	damped
Through-coolant	yes

Type of product

Boring bar shanks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/265076-32/416>
