Garant

Vario Plus Eco blade carrier, convex for face grooving, left-hand, ∅ range for groove D1 / D2: 26/39mm

Order data

Order number	274517 26/39
GTIN	4067263935230
Item class	21U

Description

Version:
Optimised system stability thanks to multiple screw clamping and form fit.
Suitable for:
Toolholder No. 274500 – 274503, 274530, 274531.
Attention:
Without clamping screws (these are supplied with the toolholders).
Note:
D_1 = minimum ∅ for the first first groove / D_2 = minimum ∅ for the second groove.

Technical description

maximum cutting depth t_{max}	18 mm
Series	Vario plus Eco
maximum 1st groove ∅ D_2	39 mm
minimum 1st groove ∅ D_1	26 mm

suitable indexable insert	No. 273664 – 273786
Application type	left-hand
Through-coolant	yes
Groove width w	3 mm
Type of product	Cartridges