

Computer workstation with printer flap, mobile, Type: FR



Order data

Order number	948262 FR
GTIN	4062406074609
Item class	9GS

Description

Version:

Computer cabinet with separately lockable double-leaf door with polycarbonate window or with printer flap. Fitted with partition for the tower compartment with galvanised storage shelf, pull-out shelf (load capacity 45 kg) with strain relief. Keyboard drawer with recessed and removable storage tray, palm rest made from bamboo and strain relief. Locking with a common key. Cable pass-through on the rear of the housing. Storage shelf made of bamboo.

With mobile base composed of 2 fixed wheels and 2 electrically conductive castors with brakes Ø 125 mm and push handles.

With space-saving TFT monitor housing for flat screens, lockable, with storage compartment for cables. Self-supporting steplessly adjustable lift door with polycarbonate window.

Colour:

Body and keyboard drawer RAL 7035 light grey, doors, drawer front and pull-out shelf RAL 7016 anthracite **powder-coated**.

Technical description

Monitor housing usable height	460 mm
Depth	700 mm

Data sheet

Height	1770 mm
Width in G	40
Weight	120 kg
Width	1000 mm
Monitor housing usable depth	230 mm
Dimensions printer flap	346×290 mm
Monitor housing usable width	690 mm
Depth in G	28
Support cabinet usable width right	223 mm
Support cabinet usable width left	700 mm
Support cabinet usable height	645 mm
Nominal voltage	250 V
#Plug type, input	E
On/Off switch	yes
Material thickness	0.9 mm
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Computer workstation

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/948262-FR>