



### FlexxTower mobile scaffolding, Platform height: 2100mm



#### Order data

|              |               |
|--------------|---------------|
| Order number | 966305 2100   |
| GTIN         | 4031405951013 |
| Item class   | 98G           |

#### Description

##### Version:

Mobile scaffolding made of stable aluminium round tube with welded frame parts. With aluminium toe boards and powder-coated guardrail frames with integrated knee bar for fall protection. Using a 3-T method, simple and safe assembly and disassembly from level to level by one person, use up to 2 persons. Tool-free installation thanks to plug connectors and quick-release fasteners. Low weight of the individual parts enables easy handling as well as space-saving transport and storage. Individual parts can be stacked compactly in one another and used as a tool trolley. With hinged triangular cantilevers with swivel base for high flexibility and stability – ideal also for wall-side construction or for moving in narrow aisles. Including 4 swivel castors Ø 125 mm, with parking brake, centric weight distribution and spindles. Height adjustment with level compensation.

##### Standard:

DIN EN 1004 load class/scaffolding group 3, load capacity up to 2.0 kN/m<sup>2</sup>.

#### Technical description

|                        |       |
|------------------------|-------|
| Working height approx. | 4.1 m |
| Scaffolding height     | 3.3 m |

## Data sheet

|                                     |                 |
|-------------------------------------|-----------------|
| Platform height                     | 2100 mm         |
| wheeled                             | yes             |
| Number of wheels                    | 4               |
| Platform width                      | 1200 mm         |
| Platform depth                      | 600 mm          |
| Weight                              | 80 kg           |
| Transport dimension                 | 1400×800×700 mm |
| Ladders and platforms load capacity | 200 kg          |
| Type of product                     | Scaffolding     |