

Garant**GARANT Master Mute boring bar shank PSC vibration damping, PSC 63,
Shank Ø / usable length L1: 16/96mm****Order data**

Order number	265064 16/96
GTIN	4069515026802
Item class	29E

Description**Version:**

With modular interface, suitable for systems from other manufacturers (e.g. Iscar).

Shank version Ø 50 mm and Ø 60 mm in right-hand version. Left-hand version available on request.

Suitable for:

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

Note:

The usable length is extended by the length L of the respective interchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

Technical description

Shank Ø	16 mm
Overhang dimension A	134 mm
Assembly bolt set	269026 1
Reach L ₁	96 mm
Series	Master Mute
Number of coolant channels	3
Adapter	PSC 63
Vibration	damped

Data sheet

Arbor standard	ISO 26623-1
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar shanks