



## Value pack LED torch with batteries



### Order data

Order number	GG1437 BLACK
GTIN	4067263137931
Item class	GGN

### Description

**Version:**

High-quality, long-life and sturdy LED torch of anodised aluminium. **Latest LED technology** with **outstanding lighting power**.

- **Anti-roll protection.**
- **Rubber cover for the operating button.**

With **focussable** lamp head.

In various colours.

**Feature:**

Contents: 5 pieces

**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

### Technical description

Illumination time stage 2	12 h
Bulb	LED module

#Number of batteries contained	15
Illumination	250 lm
Battery type	Micro, AAA
Torch function	Focus
Overall length	143 mm
Power supply	Battery-powered
ATEX zone	None
Illumination step 2	100 lm
IP Index of Protection	IP 54
Colour of housing	BLACK
Illumination time	4 h
Head Ø	27 mm
Including belt pocket	no
Type of product	Flashlight

## Accessories

LED torchwith batteries Colour BLACK	081437 BLACK
Battery holder Version 3AAA	081506 3AAA
Alkaline-manganese batteries International size LR3	081551 LR3
Alkaline-manganese batteries International size LR3	081552 LR3
Alkaline-manganese batteries International size LR3	081553 LR3
Alkaline-manganese batteries International size LR3	081554 LR3
Lithium-metal batteries International size LR3	081559 LR3
Alkaline-manganese batteries International size LR3	081561 LR3