

Garant GRIDLINE

Support leg with castors, Height: 800mm



Order data

Order number	927006 800
GTIN	4062406107703
Item class	9GG

Description

Version:

Of steel hollow section, 50 mm wide with cross bracing and mounting for height adjustment at 25 mm intervals. Feet with plastic pads, do not damage the floor. With cable slots - for simple and professional routing of media cables / power cables.

Supplied with:

Support leg No. 927000, set of braked castors No. 927202 size 2.

Colour:

Light grey RAL 7035, **powder-coated**.

Note:

Support legs without rear panel or cupboards require stabilising plates No. 927122 for stiffening. The height is to the underside of the worktop. Pre-assembled workbenches must be secured against tipping.

Technical description

Height	800 mm
Width	50 mm
Depth	700 mm

suitable for worktop depth	750 mm
Design version	Steel hollow section construction
Material thickness	1.5 mm
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Type of product	Support leg

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/927006-800>