Garant

Vario Plus Eco blade carrier, convex for face grooving, right-hand, ∅ range for groove D1 / D2: 41/53mm



Order data

Order number	274512 41/53
GTIN	4067263934981
Item class	21U

Description

Version:
Optimised system stability thanks to multiple screw clamping and form fit.
Suitable for:
Toolholder No. 274500 – 274503, 274530, 274531.
Attention:
Without clamping screws (these are supplied with the toolholders).
Note:
D_1 = minimum ∅ for the first first groove / D_2 = minimum ∅ for the second groove.

Technical description

minimum 1st groove ∅ D_1	41 mm
maximum cutting depth t_{max}	16 mm
maximum 1st groove ∅ D_2	53 mm
Series	Vario plus Eco

suitable indexable insert	No. 273664 – 273786
Application type	right-hand
Through-coolant	yes
Groove width w	2 mm
Type of product	Cartridges