

**Compressed air and liquid blow gun, adjustable Air connection, Type: FLOW****Order data**

Order number	080265 FLOW
GTIN	7391390475367
Item class	08A

Description**Version:**

Compressed air guns with steplessly adjustable air flow, low weight, flexible suspension options, and easy handling.

Compressed air and liquid blow gun with jet nozzle, **adjustable jet** (point to flat), **controllable flow** (air: 200 - 1200 ltr/min, liquid: 7 – 46 ltr/min). Complies with ISO standard B.

Supplied with steel coupling adapter No. 080300.

Note:

The CEJN series 310 is suitable for the markets of Benelux, France, North America and Norway.

Technical description

Flow rate	200 - 1200 l/min
Liquid flow rate	7 - 46 l/min
Air flow rate	200 - 1200 l/min
Type of product	Pistol

