



Electrical angle grinder CG, M14 grinding spindle thread, for 125 mm discs Ø, with restart inhibit, with anti-vibration handle



Order data

Order number	077111 722174
GTIN	4014586875125
Item class	03F

Description

Version:

FEIN – Compact angle grinder Ø 125 mm.

- **Robust, powerful motor for everyday use.**
- **High level of protection for the user thanks to recoil monitoring, restart inhibit and anti-vibration handle.**
- **High overload capability thanks to direct motor cooling; grinding head can be rotated in 90° steps (optimum switch position for the application).**
- **Grinding media can be changed quickly without the need for tools thanks to the quick-release clamping nut.**

Supplied with:

Handle, safety guard, clamping nut, wrench.

Technical description

Special features	Short body
maximum cutting depth	33 mm
Weight	2 kg

Data sheet

Power consumption	800 W
maximum vibration to EN	5 m/s ²
Restart block	yes
maximum disc Ø	125 mm
Dead man's circuit	no
Manufacturer's designation	WSG 8-125
Power supply	Mains operated
Type of product	Angle grinder