

**Garant****GARANT Master Mute boring bar shank PSC vibration damping, PSC 63,  
Shank Ø / usable length L1: 60/330mm****Order data**

Order number	265064 60/330
GTIN	4069515026956
Item class	29E

**Description****Version:**

**With modular interface, suitable for systems from other manufacturers (e.g. Iscar).**

Shank version Ø 50 mm and Ø 60 mm in right-hand version. Left-hand version available on request.

**Suitable for:**

GARANT Master Mute interchangeable cutting heads No. 265100 – 265377.

**Note:**

The usable length is extended by the length L of the respective interchangeable cutting head. Use **only with internal cooling** (temperature resistance of up to max. 100°C).

**Technical description**

Shank Ø	60 mm
Overhang dimension A	368 mm
Assembly bolt set	269026 3
Reach L <sub>1</sub>	330 mm
Series	Master Mute
Number of coolant channels	1
Adapter	PSC 63
Vibration	damped

## Data sheet

Arbor standard	ISO 26623-1
Arbor standard	ISO 12164-3
Through-coolant	yes
Type of product	Boring bar shanks