



## Oscillating saw and mitre saw BITURBO Rechargeable battery, Type: GCM18V305



### Order data

Order number	P07823 GCM18V305
GTIN	3165140965545
Item class	03B

### Description

#### Version:

**The combination of impressive cutting performance and fully wireless flexibility**

- **The brushless motor, powered by a ProCORE18V rechargeable battery, delivers wireless power equivalent to a wired 2,000 W oscillating saw and mitre saw.**
- **User interface and connectivity for checking the battery charge status, speed preselection including ECO mode.**
- **Tool-free saw blade changing; front tilt adjustment; motor brake; space-saving glide arm for safe and comfortable operation.**

#### Product highlights

The cordless oscillating saw and mitre saw GCM 18V-305 GDC Professional BITURBO offers a powerful cutting depth with cuts of up to 120 mm. The brushless motor of the oscillating saw and mitre saw has been extensively optimised for ProCORE18V technology and delivers cordless performance equivalent to that of a 2,000 W cable device. This saw offers a user interface and connectivity for quickly checking the battery charge status as well as speed preselection including ECO mode. Features such as tool-free saw blade changing, front tilt adjustment and motor brake ensure more safety when sawing.

#### Equipment and application

The tool is ideal for mitre cuts and a variety of materials. The saw can be mounted on a wide range of Bosch GTA work tables. This oscillating saw and mitre saw is compatible with all

Bosch Professional 18V rechargeable batteries and chargers (Professional 18 V system); use ProCORE18V  $\geq 5.5$  Ah for maximum power. Also compatible with AMPShare, the cross-brand battery alliance.

### Additional information

The GCM 18V-305 GDC Professional delivers full performance with just one rechargeable battery, even in difficult applications. Speed preselection and the wide range of Bosch saw blades make this oscillating saw and mitre saw perfect for working with almost any material.

### Supplied with:

- **1 pc. Bluetooth® Low Energy module GCY 42 Professional.**
- **cardboard**
- **Dust bag**
- **SDS saw blade locking**
- **Terminal**
- **Insert plate**
- **1 x saw blade, Expert for Wood, 305 x 2.2 / 1.6 x 30 mm, 60**
- **Internal hexagon drive**

**Supplied without rechargeable battery and charger.**

## Technical description

Width	630 mm
maximum mitre angle left	52 degrees
Type of rechargeable battery	Lithium-ion
Saw blade bore Ø	30 mm
maximum inclination angle right	47 degrees
Battery voltage	18 V
Power supply	Mains operated
Number of rechargeable batteries contained	0
Width of cut	341 at 0° mm
Height	790 mm
Soft start	yes
Saw blade Ø	305 mm
maximum inclination angle left	47 degrees
Weight	26.9 kg
Length	565 mm
maximum speed	4000 min <sup>-1</sup>

Data sheet

Manufacturer's designation	GCM18V305
maximum mitre angle right	60 degrees
Type of product	Saw